

NeutraForm

Automated Neutralization Device

Why incinerate when you have a Eco-Friendly Solution

Down the drain disposal of your Formalin Waste is Possible with Neutraform

Waste Tank
Cross Sectional View

No waste storage needed,
on-site treatment of formaldehyde
waste

Continuous operation
patented technology for neutralizer

NeutraForm

GERI	X	CIK	
Ym/aa	Islem	Formul	H2C
12/ 1	-	-	-
12/ 2	-	-	-
12/ 3	-	-	-
12/ 4	-	-	-
12/ 5	-	-	-
12/ 6	-	-	-
12/ 7	-	-	-
12/ 8	-	-	-
12/ 9	-	-	-
12/10	-	-	-
Toplam :			11 44 225
10:20 / 15.02.2012 / Filtre: 180 Gur			

BAYGEN

Run reports for quality control

Neutralizer

Safe and Certified Technology for neutralization of formalin waste.

Reliability of Results




Thanks to taking sample, before the neutralized waste is given to sewage enables you to check the accuracy of the procedure implemented.

TekEquipment™

Ph: 1300 368 138

www.tekequipment.com.au

info@tekequipment.com.au



NeutraForm

Automated Neutralization Device

Features

- System consists of a main unit and waste reservoirs.
- All procedures can be monitored on the main screen.
- Modularity up to four waste reservoirs.
- When any waste reservoir is full, formalin waste is transferred to main unit automatically.
- Before beginning neutralization process, the presence of neutralization material is checked by the device. In the event of absence, the user is warned audible and visually.
- After neutralizer loading, device automatically locks loading section in terms of user and application safety.
- Neutralization process is completed within approximately 30 minutes.
- Thanks to get sample, the reliability of every run can be tested.
- When procedure is completed, neutralized waste is drained to sewage as automatically.
- Run reports are monitored on the screen on daily, monthly and yearly basis.
- Change period of active carbon filter can be monitored on the screen.

Related Products

Neutralex : Neutralex is the only acceptable aldehyde neutralizer that meets the State of California EPA's requirements for safe and effective drain disposal of 10% formalin waste.

Neutralex Formalin Test Kit: Fast and reliable determination of pH, formaldehyde, glutaraldehyde and paraformaldehyde in wastewater.

Neutra-Form : For accidental spills, this fast, effective control agent diminishes harmful vapors and neutralizes hazardous aldehydes.



General Characteristics

- Fully automated
- Continuous operation
- Neutralization of 25 lt formalin waste for each run
- Possibility of taking samples
- Reporting screen
- Safe and effective drain disposal with no drain clogging solids

Environmental Requirements

- Room Temperature: 20-40 °C
- Humidity: 10% to 90%, non-condensing

Electrical Specifications

- Voltage: 115V - 230V
- Current: 8A
- Frequency: 50-60Hz

Accessories

- Carbon Filter: 10x3x25 cm (WxDxH)
- Permanganate Filter: 10x3x25 cm (WxDxH)

Models

04-0005